#### **Aldex Ion Exchange Resins**

# **Operating Temperature Guidelines**

Ion exchange resins should be used at optimal temperatures for best results. In particular when the operating teperature is too high, a degradation of exchange capacity will occur. Use the following charts to determine the maximum operating temperature for your resin type. These profiles will be affected by system variables such as the level of dissolved oxygen and the presence of catalytic metals on the resin. Therefore, we can only provide this information as guidelines and not fixed specifications.

Contact us to discuss your specific circumstances if more detail is required.

## **Strong Acid Cation Resins**

Resin Type	Na-form Maximum	H-form maximum		
8% Gel	125°C (260°F)	120°C (250°F)		
10% Gel	135°C (130°F)	130°C (265°F)		
Macroporous	150°C (300°F)	150°C (300°F)		

### **Strong Base Anion Resins**

•		
Resin Type	CI-form Maximum	OH-form maximum
Туре І	100°C (212°F)	60°C (140°F)
Type II	70°C (160°F)	35°C (95°F)
Acrylic	50°C (120°F)	35°C (95°F)

Weak Functionality Resins			
Resin Type	Maximum		
Weak Base Anion	100°C (212°F)		
Weak Acid Cation	40°C (100°F)		

## Profile for Type I Strong Base Anion Resin



ALDEX aldexchemical.com

Aldex Chemical Company, Ltd. • 630 Laurent Street • Granby QC Canada J2G 8V1 450 372 8844 • Fax 450 372 2566 • info@aldexchemical.com

These suggestions and data are based on information we believe to be reliable. They are offered in good faith. However, we do not make any guarantee or warranty. We caution against using these products in an unsafe manner or in violation of any patents. Further, we assume no liability for the consequences of such actions.